



Pass and Seymour
20A 125/250V 14-20R Straight Blade Single Flush Receptacle, 3-Pole, 4-Wire
Part No. 3820

Straight Blade Receptacle 3-Pole 4-Wire 20A 125/250V



Features & Benefits

Quality Materials.

Durability.

Time-tested Design.

Specifications

General Info

Product Line	Pass & Seymour	Color	Black
UPC Number	785007790108	Country Of Origin	Mexico
Number of Receptacles	1	Features	Durable
Outlet Type	Straight Blade	Application Sector	Multi-Dwelling Unit, Residential
Wall Plate Included	No	Standard	UL 498
Warranty Type	1-Year Limited Warranty		

Dimensions

Product Depth US	1.23 in	Product Height US	2.2 in
------------------	---------	-------------------	--------

Technical Information

Number of Wires	4	Amperage	20 A
-----------------	---	----------	------

Number of Poles	3-Way	Indoor/Outdoor	Indoor
NEMA Configuration Code	14-20	Wire Connection Type	Screw Terminals
Voltage	125/250 V		