



Pass and Seymour
30A 125V TT30 Straight Blade Single Flush Receptacle, 3-Pole, 3-Wire
Part No. 3830



Straight Blade Receptacle 2-Pole 3-Wire 30A 125A

Features & Benefits

Quality Materials.

Durability.

Time-tested Design.

Specifications

General Info

Product Line	Pass & Seymour	Color	Black
UPC Number	785007790405	Country Of Origin	China
Number of Receptacles	1	Features	Durable
Outlet Type	Straight Blade	Application Sector	Commercial
Wall Plate Included	No	Standard	UL 498
Warranty Type	1-Year Limited Warranty		

Dimensions

Product Width US	2.5 in	Product Depth US	1.9 in
Product Height US	3.75 in		

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	cULus ListingNumber	140596
cULus Listed	Yes	CSA File Number	140596

Technical Information

Connection Location	Side Only	Number of Wires	3
Amperage	30 A	Number of Poles	3-Way
Wire Size	#10 - #6 AWG	Indoor/Outdoor	Indoor
NEMA Configuration Code	NEMA TT30	Voltage	125.0 V