



Pass and Seymour
Power Outlet Receptacle Openings, One Gang, Ivory
Part No. 384I



One Gang Power Outlet Receptacle Opening, 2.156 hole for 2.125 diameter device -2 mtg. holes, Ivory, Thermoset.

Features & Benefits

Molded of non-combustible mar-proof material.	Available in 'SP' series in Standard, Junior-Jumbo, and Jumbo sizes.
Seven standard colors available -- Ivory, White, Brown, Gray, Black, Red, and Light Almond.	Individually wrapped with color-matching screws.
Resistant to discoloration, grease, oil, solvent, and moisture.	Nominal thickness, .070 inch.

Specifications

General Info

Product Line	Pass & Seymour	Color	Ivory
Finish	Matte	UPC Number	785007384017
Country Of Origin	Mexico	Material	Plastic
Construction	Plastic	Wall Plate Type	Outlet, Round
Application Sector	Commercial, Residential	Standard	UL Listed
Warranty Type	1-Year Limited Warranty		

Dimensions

Product Width US	2.75 in	Product Weight US	0.108 lb
Product Volume US	0.866 cu in	Product Depth US	0.07 in

Product Height US	4.5 in
-------------------	--------

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	CSA File Number	143222
------------	-----	-----------------	--------

Additional Information

Product Environmental Profile	Yes
-------------------------------	-----

Technical Information

Thickness	0.07 in	Number of Gangs	1
Indoor/Outdoor	Indoor	Mounting Type	Box Mounted