



Pass and Seymour
50A 250V 6-50R Straight Blade Single Surface Receptacle, 2-Pole, 3-Wire
Part No. 3852



Straight Blade Receptacle 2-Pole Wire 50A 250V

Features & Benefits

Quality Materials.

Durability.

Time-tested Design.

Specifications

General Info

Product Line	Pass & Seymour	Color	Black
UPC Number	785007791853	Country Of Origin	China
Features	Durable	Outlet Type	Straight Blade
Application Sector	Multi-Dwelling Unit, Residential	Wall Plate Included	No
Standard	UL 498	Warranty Type	1-Year Limited Warranty

Dimensions

Product Width US	2.8 in	Product Depth US	2.41 in
Product Height US	5.65 in		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140596	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Connection Location	Bottom	Number of Wires	3
Amperage	50 A	Number of Poles	Double Pole
Voltage	250.0 V		
