



Pass and Seymour
50A 125/250V 14-50R Straight Blade Single Surface Receptacle, 3-Pole, 4-Wire
Part No. 3854



Straight Blade Power Outlet Surface Receptacle, Range50A 125/250V

Features & Benefits

Quality Materials.

Durability.

Time-tested Design.

Specifications

General Info

Product Line	Pass & Seymour	Color	Black
UPC Number	785007792508	Country Of Origin	China
Number of Receptacles	1	Features	Durable
Outlet Type	Straight Blade	Application Sector	Multi-Dwelling Unit, Residential
Wall Plate Included	No	Standard	UL 498
Warranty Type	1-Year Limited Warranty		

Dimensions

Product Width US	2.8 in	Product Depth US	2.41 in
Product Height US	5.65 in		

Technical Information

Number of Wires	4	Amperage	50 A
-----------------	---	----------	------

Number of Poles	3-Way	Indoor/Outdoor	Indoor
NEMA Configuration Code	14-30	Voltage	125/250 V