

Straight Blade Receptacle 60A 120/208V



Features & Benefits

Quality Materials.

Durability.

Time-tested Design.

Specifications

General Info

Product Line	Pass & Seymour	UPC Number	785007803709
Country Of Origin	China	Number of Receptacles	1
Features	Durable	Outlet Type	Straight Blade
Application Sector	Industrial, Multi-Dwelling Unit, Residential	Wall Plate Included	No
Standard	UL 498	Warranty Type	1-Year Limited Warranty

Dimensions

Product Width US	2.5 in	Product Depth US	2.2 in
Product Height US	3.75 in		

Technical Information

Phase	4	Number of Wires	4
-------	---	-----------------	---

Amperage	60 A	Number of Poles	4-Way
Wire Size	8 - 4 AWG	Indoor/Outdoor	Indoor
NEMA Configuration Code	18-20	Voltage	120/208 V