



Pass and Seymour
50A 125/250V 10-50R Straight Blade Single Flush Receptacle, 3-Pole, 3-Wire
Part No. 3890



Straight Blade Receptacle 50A 125/250V 3-Pole 3-Wire

Features & Benefits

Quality Materials.

Durability.

Time-tested Design.

Specifications

General Info

Product Line	Pass & Seymour	Color	Black
UPC Number	785007807202	Country Of Origin	China
Number of Receptacles	1	Features	Durable
Outlet Type	Straight Blade	Application Sector	Multi-Dwelling Unit, Residential
Wall Plate Included	No	Standard	UL 498
Warranty Type	1-Year Limited Warranty		

Dimensions

Product Width US	2.5 in	Product Depth US	1.9 in
Product Height US	3.75 in		

Technical Information

Number of Wires	3	Amperage	50 A
-----------------	---	----------	------

Number of Poles	3-Way	Indoor/Outdoor	Indoor
NEMA Configuration Code	10-50R	Voltage	125/250 V