



Pass and Seymour
50 Amp 125/250V NEMA 14-50R Flush Mount Electrical Outlet for Ranges / Dryers
Part No. 3894



A durable solution that provides 50A 125/250V NEMA 14-50R power access for ranges and dryers. A single, flush-mount, straight-blade receptacle. 3-Pole, 4-Wire

Features & Benefits

Provides 50A 125/250V power access for ranges, dryers and more; NEMA compliant.	Quality Materials.
Durability.	Time-tested Design.

Specifications

General Info

Product Line	Pass & Seymour	Color	Black
UPC Number	785007807905	Country Of Origin	China
Number of Receptacles	1	Outlet Type	Straight Blade
Application Sector	Multi-Dwelling Unit, Residential	Wall Plate Included	No
Warranty Type	1-Year Limited Warranty		

Dimensions

Product Width US	2.5 in	Product Depth US	2.2 in
------------------	--------	------------------	--------

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	cULus ListingNumber	140596
cULus Listed	Yes	CSA File Number	140596

Technical Information

Operating Temperature Min	-40 °C	Connection Location	Side Only
Number of Wires	4	Operating Temperature Max	75 °C
Amperage	50 A	Number of Poles	3 Pole
Wire Size	#10 - #6 AWG (Copper), Up to #3 AWG (Aluminum)	Indoor/Outdoor	Indoor
NEMA Configuration Code	NEMA 14-50	Operating Temperature	-40°-75°C
Wire Connection Type	Screw Terminals	Voltage	125/250 V