



Pass and Seymour
30A 250V 15-30R Straight Blade Single Flush Receptacle, 3-Pole, 4-Wire
Part No. 5740



Straight Blade Receptacle 3-Pole 4-Wire 30A 250V

Features & Benefits

Quality Materials.

Durability.

Time-tested Design.

Specifications

General Info

Product Line	Pass & Seymour	UPC Number	785007574005
Country Of Origin	China	Number of Receptacles	1
Features	Durable	Outlet Type	Straight Blade
Application Sector	Commercial, Multi-Dwelling Unit, Residential	Wall Plate Included	No
Standard	UL 498	Warranty Type	1-Year Limited Warranty

Dimensions

Product Width US	2.5 in	Product Depth US	2.2 in
Product Height US	3.75 in		

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	cULus ListingNumber	140596
------------	-----	---------------------	--------

cULus Listed	Yes	CSA File Number	140596
--------------	-----	-----------------	--------

Technical Information

Number of Wires	4	Amperage	30 A
Number of Poles	3-Way	Wire Size	14 - 10 AWG
Indoor/Outdoor	Indoor	NEMA Configuration Code	15-30
Voltage	250.0 V		