



Single-Pole Switch, 15A, 120 volts

Features & Benefits

High impact resistant injection molded Thermoplastic

Back and side wire termination options accepts #14-#10AWG solid & stranded wires, Copper-clad aluminum, and copper wire

Specifications

General Info

Product Line	Pass & Seymour	Color	Black
Finish	Satin	UPC Number	785007660029
Country Of Origin	China	Material	Thermoplastic
Features	Extra Long Strap	Switch Type	Toggle
Number of Switches	1	Application Sector	Hospitality, Residential
Wall Plate Included	No	Standard	UL 498
Warranty Type	1-Year Limited Warranty	Type	Switch

Dimensions

Product Width US	1.25 in	Product Depth US	1.09 in
Product Height US	4.195 in		

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	cULus ListingNumber	140597
cULus Listed	Yes	CSA File Number	140597

Additional Information

Product Environmental Profile	Yes
-------------------------------	-----

Technical Information

Load Rating	15 A @ 120 VAC	Connection Location	Back and Side
Terminal Accommodation	#14 AWG - #10 AWG	Number of Gangs	1
Throw Type	Single Throw	Amperage	15 A
Number of Poles	Single Pole	Requires Neutral Wire	No
Indoor/Outdoor	Indoor	Mounting Type	Wall Box
Location Rating	Dry	Wire Connection Type	Push Wire
Voltage	120.0 V	Load Type	CFL, Fluorescent, Halogen, Incandescent, LED, Universal, Xenon