



Single-Pole Switch, 15A, 120 volts

## Features & Benefits

High impact resistant injection molded Thermoplastic

Back and side wire termination options accepts #14-#10AWG solid & stranded wires, Copper-clad aluminum, and copper wire

## Specifications

### General Info

|                     |                         |                    |                          |
|---------------------|-------------------------|--------------------|--------------------------|
| Product Line        | Pass & Seymour          | Color              | Ivory                    |
| Finish              | Satin                   | UPC Number         | 785007660074             |
| Country Of Origin   | China                   | Material           | Thermoplastic            |
| Features            | Extra Long Strap        | Switch Type        | Toggle                   |
| Number of Switches  | 1                       | Application Sector | Hospitality, Residential |
| Wall Plate Included | No                      | Standard           | UL 498                   |
| Warranty Type       | 1-Year Limited Warranty | Type               | Switch                   |

### Dimensions

|                   |          |                  |         |
|-------------------|----------|------------------|---------|
| Product Width US  | 1.25 in  | Product Depth US | 1.09 in |
| Product Height US | 4.195 in |                  |         |

### Listing Agencies / 3rd Party Agencies

|              |     |                     |        |
|--------------|-----|---------------------|--------|
| CSA Listed   | Yes | cULus ListingNumber | 140597 |
| cULus Listed | Yes | CSA File Number     | 140597 |

Additional Information

|                               |     |
|-------------------------------|-----|
| Product Environmental Profile | Yes |
|-------------------------------|-----|

Technical Information

|                        |                   |                       |                                                                |
|------------------------|-------------------|-----------------------|----------------------------------------------------------------|
| Load Rating            | 15 A @ 120 VAC    | Connection Location   | Back and Side                                                  |
| Terminal Accommodation | #14 AWG - #10 AWG | Number of Gangs       | 1                                                              |
| Throw Type             | Single Throw      | Amperage              | 15 A                                                           |
| Number of Poles        | Single Pole       | Requires Neutral Wire | No                                                             |
| Indoor/Outdoor         | Indoor            | Mounting Type         | Wall Box                                                       |
| Location Rating        | Dry               | Wire Connection Type  | Push Wire                                                      |
| Voltage                | 120.0 V           | Load Type             | CFL, Fluorescent, Halogen, Incandescent, LED, Universal, Xenon |