



Pass and Seymour
Trademaster® Grounding Toggle Switch, White
Part No. 664WG

Four-Way Switch, Grounded Terminals, 15 amps, 120 volts, Brown.



Features & Benefits

Back and side wire termination options accepts #14-#10AWG solid & stranded wires, Copper-clad aluminum, and copper wire

Tri-drive ground, terminal, and mounting screws.

Easy-access green hex head ground screw.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Finish	Satin	UPC Number	785007664027
Country Of Origin	Mexico	Material	Thermoplastic
Features	Extra Long Strap	Switch Type	Toggle
Number of Switches	1	Application Sector	Hospitality, Residential
Wall Plate Included	No	Standard	UL 498
Warranty Type	1-Year Limited Warranty	Type	Switch

Dimensions

Product Width US	1.25 in	Product Depth US	1.09 in
------------------	---------	------------------	---------

Product Height US	4.195 in
-------------------	----------

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	cULus ListingNumber	140597
cULus Listed	Yes	CSA File Number	17446

Additional Information

Product Environmental Profile	Yes
-------------------------------	-----

Technical Information

Load Rating	15 A @ 120 VAC	Connection Location	Back and Side
Terminal Accommodation	#14 AWG - #10 AWG	Number of Gangs	1
Amperage	15 A	Number of Poles	4-Way
Requires Neutral Wire	No	Indoor/Outdoor	Indoor
Mounting Type	Wall Box	Location Rating	Dry
Wire Connection Type	Push Wire	Voltage	120.0 V
Load Type	CFL, Fluorescent, Halogen, Incandescent, LED, Universal, Xenon		