



Pass and Seymour
Two Grounding Single-Pole Combination Switches, Light Almond
Part No. 670LAG

Single-Pole, Double Combination Switch, 20A, 120/277V, White.



Features & Benefits

Easily accessible break-off separate or common feed.

Long-life red neon lamp in pilot light rated 1/25 Watt, 125V.

Side wire #12 and #14 AWG.

Two devices fit into the space of one.

Grounding combination devices meet NEC Tamper-resistant version features dual mechanical shutter system to help prevent insertion of foreign objects.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Color	Light Almond
Finish	Satin	UPC Number	785007006032
Country Of Origin	Mexico	Material	Thermoplastic
Features	Combination	Switch Type	Toggle
Number of Switches	2	Application Sector	Hospitality, Residential
Wall Plate Included	No	Standard	UL20
Warranty Type	1-Year Limited Warranty	Type	Combination

Dimensions

Product Width US	1.32 in	Product Depth US	0.94 in
Product Height US	4.06 in		
Listing Agencies / 3rd Party Agencies			
cULus ListingNumber	140597	cULus Listed	Yes
Technical Information			
Load Rating	20 A @ 120/277 VAC	Contact Configuration	N-O
Operating Cycles	30000	Connection Location	Side Only
Terminal Accommodation	#14 AWG - #12 AWG	Number of Gangs	1
Throw Type	Single Throw	Amperage	20 A
Number of Poles	Single Pole	Requires Neutral Wire	Yes
Indoor/Outdoor	Indoor	Mounting Type	Wall Box
Location Rating	Dry	Wire Connection Type	Screw Terminals
Voltage	120/277 V	Load Type	CFL, Fluorescent, Halogen, Incandescent, LED, Universal, Xenon
Environmental Conditions	Flammability: UL94 V2		