



Pass and Seymour  
Single-Pole Combination Switch and Pilot Light, White  
Part No. 692WG

Single-Pole, Single Pilot light, Combination Switch, 15A, 120/125As, White.



## Features & Benefits

Easily accessible break-off separate or common feed.

Long-life red neon lamp in pilot light rated 1/25 Watt, 125V.

Side wire #12 and #14 AWG.

Two devices fit into the space of one.

Grounding combination devices meet NEC Tamper-resistant version features dual mechanical shutter system to help prevent insertion of foreign objects.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

## Specifications

### General Info

|                     |                         |                    |                          |
|---------------------|-------------------------|--------------------|--------------------------|
| Product Line        | Pass & Seymour          | Color              | White                    |
| Finish              | Satin                   | UPC Number         | 785007006117             |
| Country Of Origin   | Mexico                  | Material           | Thermoplastic            |
| Features            | Combination             | Switch Type        | Pilot, Switch            |
| Number of Switches  | 1                       | Application Sector | Hospitality, Residential |
| Wall Plate Included | No                      | Standard           | UL20                     |
| Warranty Type       | 1-Year Limited Warranty | Type               | Combination              |

### Dimensions

|                                       |                       |                       |                                                                |
|---------------------------------------|-----------------------|-----------------------|----------------------------------------------------------------|
| Product Width US                      | 1.32 in               | Product Depth US      | 1.15 in                                                        |
| Product Height US                     | 4.06 in               |                       |                                                                |
| Listing Agencies / 3rd Party Agencies |                       |                       |                                                                |
| cULus ListingNumber                   | 140597                | cULus Listed          | Yes                                                            |
| Technical Information                 |                       |                       |                                                                |
| Load Rating                           | 15 A @ 120 VAC        | Contact Configuration | N-O                                                            |
| Operating Cycles                      | 30000                 | Connection Location   | Side Only                                                      |
| Terminal Accommodation                | #14 AWG - #12 AWG     | Number of Gangs       | 1                                                              |
| Throw Type                            | Single Throw          | Amperage              | 15 A                                                           |
| Number of Poles                       | Single Pole           | Requires Neutral Wire | Yes                                                            |
| Indoor/Outdoor                        | Indoor                | Mounting Type         | Wall Box                                                       |
| Location Rating                       | Dry                   | Wire Connection Type  | Screw Terminals                                                |
| Voltage                               | 120.0 V               | Load Type             | CFL, Fluorescent, Halogen, Incandescent, LED, Universal, Xenon |
| Environmental Conditions              | Flammability: UL94 V2 |                       |                                                                |