



Double 3-way Combination Switch, 15A, 120/277V

Features & Benefits

Easily accessible break-off separate or common feed.

Long-life red neon lamp in pilot light rated 1/25 Watt, 125V.

Side wire #12 and #14 AWG.

Two devices fit into the space of one.

Grounding combination devices meet NEC Tamper-resistant version features dual mechanical shutter system to help prevent insertion of foreign objects.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Color	Ivory
Finish	Matte	UPC Number	785007006131
Country Of Origin	Mexico	Material	Thermoplastic
Features	Combination	Switch Type	Toggle
Number of Switches	2	Application Sector	Hospitality, Residential
Wall Plate Included	No	Standard	UL20
Warranty Type	1-Year Limited Warranty	Type	Combination, Switch

Dimensions

Product Width US	1.32 in	Product Depth US	0.94 in
Product Height US	4.06 in		
Listing Agencies / 3rd Party Agencies			
cULus ListingNumber	140597	cULus Listed	Yes
Technical Information			
Load Rating	15 A @ 120/277 VAC	Contact Configuration	N-O
Operating Cycles	30000	Connection Location	Side Only
Terminal Accommodation	#14 AWG - #12 AWG	Number of Gangs	1
Throw Type	Single Throw	Amperage	15 A
Number of Poles	3-Way	Requires Neutral Wire	Yes
Indoor/Outdoor	Indoor	Mounting Type	Wall Box
Location Rating	Dry	Wire Connection Type	Screw Terminals
Voltage	120 VAC, 277 VAC	Load Type	CFL, Fluorescent, Halogen, Incandescent, LED, Universal, Xenon
Environmental Conditions	Flammability: UL94 V2		