



radiant Collection
radiant® Tamper-Resistant Outlet, Ivory
Part No. 885TRI



Take a step up from the standard. This tamper-resistant duplex outlet installs easily for the basic power every home needs, while elevating your space with the sleek, clean lines of radiant Registered for a sophisticated look. Made exclusively for use with screwless Wall Plates from the radiant Registered Collection, sold separately.

Features & Benefits

Replaces any standard outlet with ease, in as little as 10 minutes.

Features durable, high-impact resistant thermoplastic construction.

Protects children with a patented tamper-resistant shutter system that prevents improper insertion of foreign objects, complete with "invisi-shutters" for an invisible effect.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.

Back and side wire termination options accepts #14-#10AWG solid & stranded wires, Copper-clad aluminum, and copper wire

Specifications

General Info

Product Line	Pass & Seymour	Color	Ivory
Finish	Satin	UPC Number	785007861020
Country Of Origin	China	Number of Receptacles	2
Features	Decorator Style	Outlet Type	Straight Blade, Tamper-Resistant
Application Sector	Hospitality, Residential	Wall Plate Included	No
Standard	UL 498, cULus	Warranty Type	1-Year Limited Warranty

Dimensions

Product Width US	1.29 in	Product Depth US	1.0 in
------------------	---------	------------------	--------

Product Height US	4.2 in
-------------------	--------

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E140596	cULus Listed	Yes
---------------------	---------	--------------	-----

Additional Information

Product Environmental Profile	Yes
-------------------------------	-----

Technical Information

Is Tamper-Resistant	Yes	Connection Location	Back and Side
---------------------	-----	---------------------	---------------

Terminal Accommodation	#14 AWG - #10 AWG	Number of Wires	3
------------------------	-------------------	-----------------	---

Amperage	15 A	Number of Poles	Double Pole
----------	------	-----------------	-------------

Indoor/Outdoor	Indoor	NEMA Configuration Code	5-15R
----------------	--------	-------------------------	-------

Mounting Type	Box	Wire Connection Type	Push Wire
---------------	-----	----------------------	-----------

Voltage	120.0 V, 125.0 V	Environmental Conditions	95% (relative humidity, non-condensing)
---------	------------------	--------------------------	---