



radiant Collection  
radiant® Tamper-Resistant Outlet, Nickel  
Part No. 885TRNICC12



Take a step up from the standard. This tamper-resistant duplex outlet installs easily for the basic power every home needs, while elevating your space with the sleek, clean lines of radiant Registered for a sophisticated look. Made exclusively for use with screwless Wall Plates from the radiant Registered Collection, sold separately.

## Features & Benefits

Replaces any standard outlet with ease, in as little as 10 minutes.

Features durable, high-impact resistant thermoplastic construction.

Protects children with a patented tamper-resistant shutter system that prevents improper insertion of foreign objects, complete with "invisi-shutters" for an invisible effect.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.

Back and side wire termination options accepts #14-#10AWG solid & stranded wires, Copper-clad aluminum, and copper wire

## Specifications

### General Info

|                    |                          |                       |                                  |
|--------------------|--------------------------|-----------------------|----------------------------------|
| Product Line       | Pass & Seymour           | Color                 | Nickel                           |
| Finish             | Metallic                 | UPC Number            | 785007021035                     |
| Country Of Origin  | China                    | Number of Receptacles | 2                                |
| Features           | Decorator Style          | Outlet Type           | Straight Blade, Tamper-Resistant |
| Application Sector | Hospitality, Residential | Wall Plate Included   | No                               |
| Warranty Type      | 1-Year Limited Warranty  |                       |                                  |

### Dimensions

|                  |         |                  |        |
|------------------|---------|------------------|--------|
| Product Width US | 1.29 in | Product Depth US | 1.0 in |
|------------------|---------|------------------|--------|

|                   |        |
|-------------------|--------|
| Product Height US | 4.2 in |
|-------------------|--------|

Listing Agencies / 3rd Party Agencies

|                     |         |              |     |
|---------------------|---------|--------------|-----|
| cULus ListingNumber | E140596 | cULus Listed | Yes |
|---------------------|---------|--------------|-----|

Additional Information

|                               |     |
|-------------------------------|-----|
| Product Environmental Profile | Yes |
|-------------------------------|-----|

Technical Information

|                        |                   |                          |                                         |
|------------------------|-------------------|--------------------------|-----------------------------------------|
| Is Tamper-Resistant    | Yes               | Connection Location      | Back and Side                           |
| Terminal Accommodation | #14 AWG - #10 AWG | Number of Wires          | 3                                       |
| Amperage               | 15 A              | Number of Poles          | Double Pole                             |
| Indoor/Outdoor         | Indoor            | NEMA Configuration Code  | 5-15R                                   |
| Mounting Type          | Box               | Wire Connection Type     | Push Wire                               |
| Voltage                | 120.0 V, 125.0 V  | Environmental Conditions | 95% (relative humidity, non-condensing) |