



radiant Collection
Discontinued - radiant® Outdoor Outlet, Ivory
Part No. 885TRWRI



Take a step up from the standard, even outside. This weather-resistant* outlet installs easily to bring power to your patio, pool area, porch or deck, while elevating your outdoor space with the sleek, clean lines of radiant Registered for a sophisticated look. Made exclusively for use with screwless Wall Plates from the radiant Registered Collection, sold separately.

Features & Benefits

Replaces any standard outlet with ease, in as little as 10 minutes.

Features durable, high-impact resistant thermoplastic construction.

Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.

Designed with weather-resistance for use in outdoor locations such as decks, patios and pool areas. *Must be installed in weatherproof enclosure per NEC requirements.

More color options available to fit any style.

Specifications

General Info

Product Line	Pass & Seymour	Replaced by Part Number	885TREXWRI
Color	Ivory	Finish	Satin
UPC Number	785007241709	Country Of Origin	Mexico
Number of Receptacles	2	Features	Decorator Style, Weatherproof
Outlet Type	Straight Blade, Tamper-Resistant, Weather-Resistant	Application Sector	Hospitality, Residential
Wall Plate Included	No	Standard	UL 498
Warranty Type	1-Year Limited Warranty		

Dimensions

Product Width US	1.29 in	Product Depth US	1.0 in
Product Height US	4.2 in		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E140596	cULus Listed	Yes
---------------------	---------	--------------	-----

Additional Information

Product Environmental Profile	Yes
-------------------------------	-----

Technical Information

Is Tamper-Resistant	Yes	Connection Location	Back and Side
Number of Wires	3	Number of Gangs	1
Amperage	15 A	Number of Poles	Double Pole
Indoor/Outdoor	Outdoor	Mounting Type	Box
Wire Connection Type	Internal Pressure Plates, Screw Terminals	Voltage	120.0 V, 125.0 V