



Take a step up from the standard. This duplex outlet installs easily for the basic power every home needs, while elevating your space with the sleek, clean lines of radiant Registered for a sophisticated look. Made exclusively for use with screwless Wall Plates from the radiant Registered Collection, sold separately.

Features & Benefits

Replaces any standard outlet with ease, in as little as 10 minutes.

Features durable, high-impact resistant thermoplastic construction.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Finish	Satin	UPC Number	785007856392
Country Of Origin	China	Number of Receptacles	2
Features	Decorator Style	Outlet Type	Straight Blade
Application Sector	Hospitality, Residential	Wall Plate Included	No
Warranty Type	1-Year Limited Warranty		

Dimensions

Product Width US	1.29 in	Product Depth US	1.0 in
Product Height US	4.2 in		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140596	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Connection Location	Back and Side	Number of Wires	3
---------------------	---------------	-----------------	---

Number of Gangs	1	Amperage	15 A
-----------------	---	----------	------

Number of Poles	Double Pole	Indoor/Outdoor	Indoor
-----------------	-------------	----------------	--------

NEMA Configuration Code	5-15R	Wire Connection Type	Internal Pressure Plates, Screw Terminals
-------------------------	-------	----------------------	---

Voltage	120.0 V, 125.0 V
---------	------------------