



radiant Collection  
radiant® Full Night Light, White  
Part No. NTLFULLWCC6



Make nighttime navigation easier with a sleek, sophisticated built-in night light from the radiant Registered Collection. Ideal for hallways and nurseries, this Full Night Light installs easily in place of a standard outlet to save you from stumbling in the dark or transitioning to too bright overhead lights. Features five adjustable light levels, as well as an optional louver for additional light-level control. Made exclusively for use with screwless Wall Plates from the radiant Registered Collection, sold separately.

## Features & Benefits

Easily replaces any standard outlet to provide a stylish built-in night light.

Features five adjustable light settings: Ultra Low, Low, Medium, High and OFF.

Hidden sensor controls night light based on ambient light, automatically turning on when it is dark.

Features durable, high-impact resistant thermoplastic construction.

More color options available to fit any style.

Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.

## Specifications

### General Info

|                    |                          |                     |               |
|--------------------|--------------------------|---------------------|---------------|
| Product Line       | Pass & Seymour           | Color               | White         |
| Finish             | Satin                    | UPC Number          | 785007034332  |
| Country Of Origin  | China                    | Material            | Polycarbonate |
| Features           | Nightlight               | Number of Switches  | 1             |
| Application Sector | Hospitality, Residential | Wall Plate Included | No            |
| Warranty Type      | 1-Year Limited Warranty  | Type                | Nightlight    |

### Dimensions

|                  |         |                  |        |
|------------------|---------|------------------|--------|
| Product Width US | 1.29 in | Product Depth US | 1.3 in |
|------------------|---------|------------------|--------|

|                   |        |
|-------------------|--------|
| Product Height US | 4.2 in |
|-------------------|--------|

Listing Agencies / 3rd Party Agencies

|                     |         |              |     |
|---------------------|---------|--------------|-----|
| cULus ListingNumber | E234593 | cULus Listed | Yes |
|---------------------|---------|--------------|-----|

Technical Information

|                     |               |                        |                                                                |
|---------------------|---------------|------------------------|----------------------------------------------------------------|
| Connection Location | Back and Side | Terminal Accommodation | #14 AWG - #12 AWG                                              |
| Number of Gangs     | 1             | Throw Type             | Single Throw                                                   |
| Amperage            | 15 A          | Requires Neutral Wire  | Yes                                                            |
| Indoor/Outdoor      | Indoor        | Mounting Type          | Wall Box                                                       |
| Location Rating     | Dry           | Wire Connection Type   | Push Wire, Wire Terminal                                       |
| Voltage             | 120/125 V     | Load Type              | CFL, Fluorescent, Halogen, Incandescent, LED, Universal, Xenon |