



radiant Collection
radiant® 3.1A USB Outlet, Type A/C, 15A, Tamper-Resistant, White
Part No. R26USBACW



Make it easier to get a full battery for your smartphones, tablets and more with the convenience of built-in charging. A perfect charging solution for your current and future electronic devices, this tamper-resistant USB outlet features connections for USB Type-A and the newer USB Type-C. Easily replacing traditional outlets in as little as ten minutes, this outlet offers accessible charging without needing bulky adapters or sacrificing your plugs, and features the sleek, clean lines of radiant® for a sophisticated look. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.

Features & Benefits

- Provides convenient built-in charging, without sacrificing plugs or requiring a bulky adapter.
- Accommodates all mobile devices with connections for both traditional USB Type-A and the newer USB Type-C, which features a smaller, reversible connector and high-speed specs.
- All Legrand USB Outlets are manufactured through high-quality design, sourcing and production, and backed by a Lifetime Warranty.
- Protects children with a patented tamper-resistant shutter system that prevents improper insertion of foreign objects, complete with "invisi-shutters" for an invisible effect.
- Replaces a traditional outlet easily, in as little as 10 minutes.
- More color options available to fit any style, including finishes to match current hardware and lighting trends.
- Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Finish	Satin	UPC Number	785007181401
Country Of Origin	Vietnam	Number of Receptacles	2
Features	USB-A Charging, USB-C Charging	Outlet Type	Tamper-Resistant, USB-Charging
Application Sector	Hospitality, Multi-Dwelling Unit, Residential	Wall Plate Included	No
Warranty Type	Limited Lifetime Warranty		

Dimensions

Product Width US	1.693 in	Product Depth US	1.35 in
Product Height US	4.18 in		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E140596	cULus Listed	Yes
---------------------	---------	--------------	-----

Additional Information

Product Environmental Profile	Yes		
-------------------------------	-----	--	--

Technical Information

Is Tamper-Resistant	Yes	Connection Location	Back and Side
USB Wattage	15 W	USB Amperage	3.1 A
Number of USBs	2	Number of Wires	3
Amperage	15 A	Number of Poles	Double Pole
Indoor/Outdoor	Indoor	NEMA Configuration Code	5-15R
Mounting Type	Box	Wire Connection Type	Internal Pressure Plates, Screw Terminals
Voltage	5.0 V	Environmental Conditions	95% (relative humidity, non-condensing)