



radiant Collection
radiant® 30W USB Outlet, Type C, 15A, Tamper-Resistant, Brown
Part No. R26USBPD



Made to deliver a 30 Watts of power and featuring two built-in Type-C USB connections, this solution adds advanced Power Delivery to the industry-leading amperage of our USB line. The result is a faster, future-proof option for convenient in-wall charging, specially designed to optimize performance for your Power Delivery-enabled devices. Easily replace a traditional outlet in as little as ten minutes to gain the modern functionality of intelligent charging for maximized speeds, complete with multi-layered overcurrent protection to keep the outlet and your devices safe from damage. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.

Features & Benefits

Charges the latest devices up to 2X faster with 6.0 amps and 30W of power courtesy of advanced Power Delivery.	Built for intelligent charging, the outlet detects and delivers the precise amount of power needed to maximize charging speeds
Provides fast and convenient built-in charging through two future-proof USB Type-C ports, accommodating new and upcoming devices without an adapter	Helpful indicator light lets you see charging status at a glance. Light glows yellow while charging is in progress, and shows green once the device battery is sufficiently charged
Includes multiple layers of overcurrent protection, ensuring the outlet and your favorite devices can charge at optimal levels without risk of damage	All Legrand USB Outlets are manufactured through high-quality design, sourcing and production, and backed by a Lifetime Warranty
Protects children with a patented tamper-resistant shutter system that prevents improper insertion of foreign objects, complete with "invisi-shutters" for an invisible effect	Replaces a traditional outlet easily, in as little as 10 minutes, with features like scalloped cover design and posted side-wire terminal screws for faster installation
More color options available to fit any style, including finishes to match current hardware and lighting trends	

Specifications

General Info

Product Line	Pass & Seymour	Color	Brown
Finish	Satin	UPC Number	785007297737
Country Of Origin	China	Number of Receptacles	2
Features	Indicator Lights, Power Delivery, USB-C Charging	Outlet Type	Tamper-Resistant, USB-Charging

Application Sector	Hospitality, Multi-Dwelling Unit, Residential	Warranty Type	Limited Lifetime Warranty
Dimensions			
Product Width US	1.693 in	Product Depth US	1.35 in
Product Height US	4.18 in		
Listing Agencies / 3rd Party Agencies			
cULus ListingNumber	E140596	cULus Listed	Yes
Additional Information			
RoHS Compliant	Yes		
Technical Information			
Connection Location	Back and Side	USB Wattage	30 W
USB Amperage	6 A	Number of USBs	2
Number of Wires	3	Output Current	6A
Amperage	15 A	Number of Poles	Double Pole
Indoor/Outdoor	Indoor	Mounting Type	Box
Wire Connection Type	Internal Pressure Plates, Screw Terminals	Voltage	15.0 V, 5.0 V, 9.0 V
Environmental Conditions	95% (relative humidity, non-condensing)		