



radiant Collection
radiant® Two Single-Pole Switches, Gray
Part No. RCD11GRY



Control two separate lights or devices from a single location with this combination switch. Designed to emulate the sleek lines of the collection's paddle switches, it delivers flexible, space-saving control with the sophisticated look of radiant. Made exclusively for use with screwless Wall Plates from the radiant Registered Collection, sold separately.

Features & Benefits

Offers installation flexibility with space-saving style, as part of the extensive offering from the radiant® Collection. Features durable, high-impact resistant thermoplastic construction.

Designed to install easily with a narrower back body and captivated mounting screws. Patented Snap-In Light Module (sold separately) transforms a combination switch into an illuminated switch in seconds.

More color options available to fit any style, including finishes to match current hardware and lighting trends. Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.

Specifications

General Info

Product Line	Pass & Seymour	Color	Gray
Finish	Satin	UPC Number	785007233520
Country Of Origin	China	Material	Thermoplastic
Features	Combination, Decorator Style, Locator Light	Switch Type	Paddle
Number of Switches	2	Application Sector	Residential
Wall Plate Included	No	Warranty Type	1-Year Limited Warranty
Type	Switch		

Dimensions

Product Width US	1.29 in	Product Depth US	1.59 in
Product Height US	3.81 in		

Technical Information

Load Rating	15 A @ 120/125 VAC	Connection Location	Back and Side
Terminal Accommodation	#14 AWG - #12 AWG	Number of Gangs	1
Throw Type	Single Throw	Amperage	15 A
Number of Poles	3-Way, Single Pole	Requires Neutral Wire	Yes
Indoor/Outdoor	Indoor	Mounting Type	Wall Box
Location Rating	Dry	Wire Connection Type	Push Wire, Wire Terminal
Voltage	120 VAC, 125 VAC	Load Type	CFL, Fluorescent, Halogen, Incandescent, LED, Universal, Xenon