



radiant Collection
radiant® Single Pole/3-Way Switch with 15A Tamper-Resistant Outlet, Black
Part No. RCD38TRBKCC6



A step up from ordinary, this combination switch and outlet from the radiant Registered Collection provides convenience and flexibility, as well as style. Operable in both single-pole and 3-way applications, you can use it alone to control one light or fixture, or use with another 3-Way switch for controlling the light from two locations. Also includes a tamper-resistant outlet for safe access to the basic power every home needs. Part of the radiant Registered Collection, it features clean lines and a smooth finish for a sophisticated look. Made exclusively for use with screwless Wall Plates from the radiant Registered Collection, sold separately.

Features & Benefits

Replaces a standard switch/outlet with ease, in as little as 10 minutes.

Protects children with a patented tamper-resistant shutter system that prevents improper insertion of foreign objects, complete with "invisi-shutters" for an invisible effect.

More color options available to fit any style.

Offers installation flexibility, working in both single-pole and 3-way applications.

Features durable, high-impact resistant thermoplastic construction.

Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.

Specifications

General Info

Product Line	Pass & Seymour	Color	Black
Finish	Satin	UPC Number	785007055030
Country Of Origin	China	Number of Receptacles	1
Features	Combination, Locator Light	Switch Type	Push
Number of Switches	1	Outlet Type	Tamper-Resistant
Application Sector	Hospitality, Multi-Dwelling Unit, Residential	Wall Plate Included	No
Warranty Type	1-Year Limited Warranty		

Dimensions

Product Width US	1.29 in	Product Depth US	1.59 in
------------------	---------	------------------	---------

Product Height US	3.81 in		
-------------------	---------	--	--

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E140597	cULus Listed	Yes
---------------------	---------	--------------	-----

Technical Information

Is Tamper-Resistant	Yes	Connection Location	Back and Side
---------------------	-----	---------------------	---------------

Number of Wires	5	Number of Gangs	1
-----------------	---	-----------------	---

Amperage	15 A	Number of Poles	3-Way, Single Pole
----------	------	-----------------	--------------------

Wire Size	#14 - #10 AWG	Indoor/Outdoor	Indoor
-----------	---------------	----------------	--------

Mounting Type	Box	Wire Connection Type	Screw Terminals
---------------	-----	----------------------	-----------------

Voltage	120/125 V		
---------	-----------	--	--