



radiant Collection  
radiant® Single Pole/3-Way Switch with 15A Tamper-Resistant Outlet, Gray  
Part No. RCD38TRGRY



A step up from ordinary, this combination switch and outlet from the radiant Registered Collection provides convenience and flexibility, as well as style. Operable in both single-pole and 3-way applications, you can use it alone to control one light or fixture, or use with another 3-Way switch for controlling the light from two locations. Also includes a tamper-resistant outlet for safe access to the basic power every home needs. Part of the radiant Registered Collection, it features clean lines and a smooth finish for a sophisticated look. Made exclusively for use with screwless Wall Plates from the radiant Registered Collection, sold separately.

## Features & Benefits

Replaces a standard switch/outlet with ease, in as little as 10 minutes.

Protects children with a patented tamper-resistant shutter system that prevents improper insertion of foreign objects, complete with "invisi-shutters" for an invisible effect.

More color options available to fit any style.

Offers installation flexibility, working in both single-pole and 3-way applications.

Features durable, high-impact resistant thermoplastic construction.

Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.

## Specifications

### General Info

|                    |                                               |                       |                  |
|--------------------|-----------------------------------------------|-----------------------|------------------|
| Product Line       | Pass & Seymour                                | Color                 | Gray             |
| Finish             | Satin                                         | UPC Number            | 785007233582     |
| Country Of Origin  | China                                         | Number of Receptacles | 1                |
| Features           | Combination, Locator Light                    | Switch Type           | Push             |
| Number of Switches | 1                                             | Outlet Type           | Tamper-Resistant |
| Application Sector | Hospitality, Multi-Dwelling Unit, Residential | Wall Plate Included   | No               |
| Warranty Type      | 1-Year Limited Warranty                       |                       |                  |

## Dimensions

|                   |         |                  |         |
|-------------------|---------|------------------|---------|
| Product Width US  | 1.29 in | Product Depth US | 1.59 in |
| Product Height US | 3.81 in |                  |         |

Technical Information

|                     |               |                      |                    |
|---------------------|---------------|----------------------|--------------------|
| Is Tamper-Resistant | Yes           | Connection Location  | Back and Side      |
| Number of Wires     | 5             | Number of Gangs      | 1                  |
| Amperage            | 15 A          | Number of Poles      | 3-Way, Single Pole |
| Wire Size           | #14 - #10 AWG | Indoor/Outdoor       | Indoor             |
| Mounting Type       | Box           | Wire Connection Type | Screw Terminals    |
| Voltage             | 120/125 V     |                      |                    |