



radiant Collection
radiant® 20A Wave® Switch
Part No. RSWV203



When it comes to lighting control, it's time to keep your hands...or at least their messes...to yourself. Thanks to Legrand's innovative touchless technology, this sleek switch lets you turn lights on or off with a simple wave for the germ-and-worry solution that's perfect for any home's entryway or kitchen, as well as for shared spaces like offices, hotels and more. Wave ""hello"" to cleaner, more convenient control for cleaner, more convenient spaces. Made exclusively for use with the screwless Wall Plates from the radiant Registered Collection, sold separately. Made exclusively for use with screwless Wall Plates from the radiant Registered Collection, sold separately.

Features & Benefits

Features innovative touchless control for a convenient, germ-free way to turn on lights...all it takes is a simple wave

Installs easily in 15 minutes or less, fitting into an existing electrical box. Usable in both single-pole and 3-way applications

Made for use in both residential and commercial applications; features durable construction to withstand rigorous cleaning practices

Includes a rating of up to 3/4 HP for adding touchless control to small motors

Adjust the internal sensor to respond to movement from 1 to 6 inches from the switch face to fit your space and needs

Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection

Specifications

General Info

Product Line	Pass & Seymour	Color	Black
Finish	Satin	UPC Number	785007382518
Country Of Origin	China	Material	Thermoplastic
Features	Decorator Style, Touchless	Switch Type	Wave
Number of Switches	1	Application Sector	Residential
Wall Plate Included	No	Warranty Type	1-Year Limited Warranty
Type	Decorator, Switch		

Dimensions

Product Width US	1.72 in	Product Depth US	1.03 in
Product Height US	4.2 in		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Additional Information

RoHS Compliant	Yes
----------------	-----

Technical Information

Load Rating	20 A @ 120/125 VAC	Seismic Tested	No
Connection Location	Back and Side	Horsepower Rating	3/4 HP @ 120/125 VAC
Terminal Accommodation	#14 AWG - #12 AWG	Number of Gangs	1
Amperage	20 A	Number of Poles	3-Way, Single Pole
Requires Neutral Wire	Yes	Indoor/Outdoor	Indoor
Mounting Type	Wall Box	Location Rating	Dry
Wire Connection Type	Internal Pressure Plates	Voltage	120/125 V
Load Type	CFL, Fluorescent, Halogen, Incandescent, LED, Universal, Xenon		