



Pass and Seymour
2-Gang Thermoset Wall Plate, 3 Toggle Switch Opening, 1 Duplex Receptacle, Ivory
Part No. SP18I



Combination Wall Plate, 1 Toggle Switch and 1 Duplex Receptacle, 2-Gang

Features & Benefits

Molded of non-combustible mar-proof material.

Seven standard colors available -- Ivory, White, Brown, Gray, Black, Red, and Light Almond.

Resistant to discoloration, grease, oil, solvent, and moisture.

Available in 'SP' series in Standard, Junior-Jumbo, and Jumbo sizes.

Individually wrapped with color-matching screws.

Nominal thickness, .070 inch.

Specifications

General Info

Product Line	Pass & Seymour	Color	Ivory
Finish	Matte	UPC Number	785007681529
Country Of Origin	Mexico	Material	Thermoset Plastic
Construction	Plastic	Wall Plate Size	Standard Size
Wall Plate Type	Combination, Duplex Receptacle, Toggle Switch	Application Sector	Commercial, Residential
Standard	CSA, UL514	Warranty Type	1-Year Limited Warranty
Type	Wall Plate		

Dimensions

Product Width US	4.56 in	Product Depth US	0.2 in
Product Height US	4.5 in		

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	CSA File Number	143222
------------	-----	-----------------	--------

Additional Information

Product Environmental Profile	Yes
-------------------------------	-----

Technical Information

Thickness	0.07 in	Number of Gangs	2
Indoor/Outdoor	Indoor	Mounting Type	Box Mounted
Orientation	Vertical		