



Pass and Seymour  
1-Gang Thermoset Wall Plate, 1 Toggle Switch Opening, Ivory  
Part No. SP1I



Plate Plastic 1-Gang Toggle Without Line

## Features & Benefits

|                                                                                                |                                                                      |
|------------------------------------------------------------------------------------------------|----------------------------------------------------------------------|
| Molded of non-combustible mar-proof material.                                                  | Available in 'SP' series in Standard, Junior-Jumbo, and Jumbo sizes. |
| Seven standard colors available -- Ivory, White, Brown, Gray, Black, Red, and Light Almond.    | Individually wrapped with color-matching screws.                     |
| Resistant to discoloration, grease, oil, solvent, and moisture.                                | Nominal thickness, .070 inch.                                        |
| For covering patents, see <a href="http://www.legrand.us/patents">www.legrand.us/patents</a> . |                                                                      |

## Specifications

### General Info

|                   |                |                    |                         |
|-------------------|----------------|--------------------|-------------------------|
| Product Line      | Pass & Seymour | Color              | Ivory                   |
| Finish            | Matte          | UPC Number         | 785007681406            |
| Country Of Origin | Mexico         | Material           | Thermoset Plastic       |
| Construction      | Plastic        | Wall Plate Size    | Standard Size           |
| Wall Plate Type   | Toggle Switch  | Application Sector | Commercial, Residential |
| Standard          | CSA, UL514     | Warranty Type      | 1-Year Limited Warranty |
| Type              | Wall Plate     |                    |                         |

### Dimensions

|                  |         |                  |        |
|------------------|---------|------------------|--------|
| Product Width US | 2.75 in | Product Depth US | 0.2 in |
|------------------|---------|------------------|--------|

---

|                   |        |
|-------------------|--------|
| Product Height US | 4.5 in |
|-------------------|--------|

---

Listing Agencies / 3rd Party Agencies

---

|            |     |                 |        |
|------------|-----|-----------------|--------|
| CSA Listed | Yes | CSA File Number | 143222 |
|------------|-----|-----------------|--------|

---

Additional Information

---

|                               |     |
|-------------------------------|-----|
| Product Environmental Profile | Yes |
|-------------------------------|-----|

---

Technical Information

---

|           |         |                 |   |
|-----------|---------|-----------------|---|
| Thickness | 0.07 in | Number of Gangs | 1 |
|-----------|---------|-----------------|---|

---

|                |        |               |               |
|----------------|--------|---------------|---------------|
| Indoor/Outdoor | Indoor | Mounting Type | Strap Mounted |
|----------------|--------|---------------|---------------|

---

|             |          |
|-------------|----------|
| Orientation | Vertical |
|-------------|----------|

---