



Pass and Seymour  
3-Gang Thermoset Wall Plate, 3 Decorator Openings, White  
Part No. SP263W



Plate Plastic 3-Gang Sierraplex Without Line

## Features & Benefits

Molded of non-combustible mar-proof material.

Available in 'SP' series in Standard, Junior-Jumbo, and Jumbo sizes.

Seven standard colors available -- Ivory, White, Brown, Gray, Black, Red, and Light Almond.

Individually wrapped with color-matching screws.

Resistant to discoloration, grease, oil, solvent, and moisture.

Nominal thickness, .070 inch.

## Specifications

### General Info

|                   |                |                    |                         |
|-------------------|----------------|--------------------|-------------------------|
| Product Line      | Pass & Seymour | Color              | White                   |
| Finish            | Matte          | UPC Number         | 785007680102            |
| Country Of Origin | Mexico         | Material           | Thermoset Plastic       |
| Construction      | Plastic        | Wall Plate Size    | Standard Size           |
| Wall Plate Type   | Decorator      | Application Sector | Commercial, Residential |
| Standard          | CSA, UL514     | Warranty Type      | 1-Year Limited Warranty |
| Type              | Wall Plate     |                    |                         |

### Dimensions

|                   |          |                  |        |
|-------------------|----------|------------------|--------|
| Product Width US  | 6.375 in | Product Depth US | 0.2 in |
| Product Height US | 4.5 in   |                  |        |

### Listing Agencies / 3rd Party Agencies

|            |     |                 |        |
|------------|-----|-----------------|--------|
| CSA Listed | Yes | CSA File Number | 143222 |
|------------|-----|-----------------|--------|

### Additional Information

|                               |     |
|-------------------------------|-----|
| Product Environmental Profile | Yes |
|-------------------------------|-----|

---

Technical Information

|                |          |                 |             |
|----------------|----------|-----------------|-------------|
| Thickness      | 0.07 in  | Number of Gangs | 3           |
| Indoor/Outdoor | Indoor   | Mounting Type   | Box Mounted |
| Orientation    | Vertical |                 |             |

---