



Pass and Seymour
4-Gang Thermoset Wall Plate, 3 Toggle Switch, 1 Duplex Receptacle, White
Part No. SP38W



This 4-gang wall plate provides opening for 3-toggle switches and 1-duplex receptacle

Features & Benefits

Molded of non-combustible mar-proof material.	Available in 'TP' series, extra 3/16 inch width and height than Standard size plates: and 'TPJ' series, extra 3/16 inch width and height than Junior-Jumbo size plates.
Seven standard colors available -- Ivory, White, Brown, Gray, Black, Red, and Light Almond.	Individually wrapped with color-matching screws.
Resistant to discoloration, grease, oil, solvent, and moisture.	Nominal thickness, .070 inch.

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Finish	Matte	UPC Number	785007187182
Country Of Origin	Mexico	Material	Thermoset Plastic
Construction	Plastic	Wall Plate Size	Standard Size
Wall Plate Type	Combination, Duplex Receptacle, Toggle Switch	Application Sector	Commercial, Residential
Standard	CSA, UL514	Warranty Type	1-Year Limited Warranty
Type	Wall Plate		

Dimensions

Product Width US	8.125 in	Product Depth US	0.2 in
Product Height US	4.5 in		

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	CSA File Number	143222
------------	-----	-----------------	--------

Additional Information

Product Environmental Profile Yes

Technical Information

Thickness	0.07 in	Number of Gangs	4
Indoor/Outdoor	Indoor	Mounting Type	Strap Mounted
Orientation	Vertical		
