



Pass and Seymour
Spec Grade Decorator Maintained Contact Switch, White
Part No. TM811DTMAW



Specification Grade, Double-Throw, Maintained Contact Switch, 15A, 120 volts.

Features & Benefits

Impact-resistant face and body.

Fully rounded back body protects wires from being damaged by sharp edges.

Clear identification of circuits.

External screw-pressure-plate back and side wired. Accepts #12 and #14 AWG.

Ground screw position under the end of the strap minimizes the risk of contact.

Full wraparound metal strap with lock-in tabs.

Patented split circuit tab -- easily accessible, and can be reinstalled without a tool.

Unique "Up/Down" switches match the look and feel of standard Decorator switches.

Largest breadth of 15 amp offering.

All screws are tri-drive.

Tamper-resistant version features dual mechanical shutter system to help prevent insertion of foreign objects.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Finish	Satin	UPC Number	785007157598
Country Of Origin	China	Material	Thermoplastic
Features	Decorator Style	Switch Type	Paddle
Number of Switches	2	Application Sector	Commercial, Residential
Wall Plate Included	No	Standard	UL 20

Warranty Type	1-Year Limited Warranty	Type	Combination, Decorator, Switch
Dimensions			
Product Width US	1.29 in	Product Depth US	1.59 in
Product Height US	3.812 in		
Listing Agencies / 3rd Party Agencies			
cULus Listed	Yes		
Technical Information			
Load Rating	15 A @ 120 VAC	Connection Location	Side Only
Terminal Accommodation	#14 AWG - #12 AWG	Number of Gangs	1
Throw Type	Double Throw	Amperage	15 A
Number of Poles	Single Pole	Requires Neutral Wire	Yes
Indoor/Outdoor	Indoor	Mounting Type	Wall Box
Location Rating	Dry	Wire Connection Type	Screw Terminals
Voltage	120.0 V	Load Type	CFL, Fluorescent, Halogen, Incandescent, LED, Universal, Xenon