



Pass and Seymour
Spec Grade Decorator Momentary Contact Switch, White
Part No. TM811DTMOW



Specification Grade, Double-Throw, Momentary Contact Switch, 15A, 120V.

Features & Benefits

Impact-resistant face and body.

Clear identification of circuits.

External screw-pressure-plate back and side wired.
Accepts #12 and #14 AWG.

Ground screw position under the end of the strap minimizes the risk of contact.

Full wraparound metal strap with lock-in tabs.

Unique "Up/Down" switches match the look and feel of standard Decorator switches.

Largest breadth of 15 amp offering.

All screws are tri-drive.

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Finish	Matte	UPC Number	785007157550
Country Of Origin	China	Features	Decorator Style
Application Sector	Commercial, Residential	Standard	UL 20
Type	Combination		

Dimensions

Product Width US	1.29 in	Product Depth US	1.59 in
Product Height US	3.812 in		

Listing Agencies / 3rd Party Agencies

cULus Listed Yes

Technical Information

Amperage	15 A	Wire Size	#14 - #10 AWG
----------	------	-----------	---------------
