



radiant Collection  
radiant® 15A Single-Pole Switch, Graphite  
Part No. TM870GCC10



The perfect upgrade for your basic light switch, the Single-Pole Switch from the radiant Registered Collection provides on/off control of a light or fixture from a single location, while combining clean lines and smooth paddle action for a sophisticated touch. Made exclusively for use with screwless Wall Plates from the radiant Registered Collection, sold separately.

## Features & Benefits

Replaces any standard switch with ease, in as little as 10 minutes

Uses a paddle switch for smoother control with a low-profile aesthetic

Features durable, high-impact resistant thermoplastic construction

Designed to install easily with a narrower back body and captivated mounting screws

More color options available to fit any style, including finishes to match current hardware and lighting trends

Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection

Back and side wire termination options accepts #14–#10AWG solid & stranded wires, Copper-clad aluminum, and copper wire

## Specifications

### General Info

|                     |                 |                    |                         |
|---------------------|-----------------|--------------------|-------------------------|
| Product Line        | Pass & Seymour  | Color              | Graphite                |
| Finish              | Metallic        | UPC Number         | 785007173697            |
| Country Of Origin   | China           | Material           | Thermoplastic           |
| Features            | Decorator Style | Switch Type        | Paddle                  |
| Number of Switches  | 1               | Application Sector | Commercial, Residential |
| Wall Plate Included | No              | Warranty Type      | 1-Year Limited Warranty |
| Type                | Switch          |                    |                         |

Dimensions

|                   |         |                  |         |
|-------------------|---------|------------------|---------|
| Product Width US  | 1.43 in | Product Depth US | 1.27 in |
| Product Height US | 4.19 in |                  |         |

Listing Agencies / 3rd Party Agencies

|                     |         |              |     |
|---------------------|---------|--------------|-----|
| cULus ListingNumber | E140597 | cULus Listed | Yes |
|---------------------|---------|--------------|-----|

Technical Information

|                        |                   |                       |                                                                |
|------------------------|-------------------|-----------------------|----------------------------------------------------------------|
| Load Rating            | 15 A @ 120 VAC    | Connection Location   | Back and Side                                                  |
| Terminal Accommodation | #14 AWG - #10 AWG | Number of Gangs       | 1                                                              |
| Throw Type             | Single Throw      | Amperage              | 15 A                                                           |
| Number of Poles        | Single Pole       | Requires Neutral Wire | No                                                             |
| Indoor/Outdoor         | Indoor            | Mounting Type         | Wall Box                                                       |
| Location Rating        | Dry               | Wire Connection Type  | Push Wire, Wire Terminal                                       |
| Voltage                | 120 VAC, 125 VAC  | Load Type             | CFL, Fluorescent, Halogen, Incandescent, LED, Universal, Xenon |