



radiant Collection
radiant® Momentary Contact Switch
Part No. TM870STMBKCC6



The radiant Registered Momentary Contact Switch is perfect anywhere you need the safety of a switch that is only on when held in the "on" position. Made exclusively for use with screwless Wall Plates from the radiant Registered Collection, sold separately.

Features & Benefits

- Part of the radiant® collection. High-impact resistant thermoplastic construction
- Narrow back body leaves more room for wires in the box. Extra-long, through-body strap eliminates floating installations and imperfect applications
- Smooth, quiet paddle action Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.

Specifications

General Info

Product Line	Pass & Seymour	Color	Black
Finish	Satin	UPC Number	785007043655
Country Of Origin	Mexico	Material	Thermoplastic
Features	Decorator Style, Momentary Contact	Switch Type	Paddle
Number of Switches	1	Application Sector	Residential
Wall Plate Included	No	Standard	CSA Listed, UL Listed
Warranty Type	1-Year Limited Warranty	Type	Switch

Dimensions

Product Width US	1.43 in	Product Depth US	1.27 in
------------------	---------	------------------	---------

Product Height US4.19 in

Listing Agencies / 3rd Party Agencies

cULus ListedYes

Additional Information

Product Environmental ProfileYes

Technical Information

Load Rating	15 A @ 120 VAC	Operating Cycles	50000
Connection Location	Back and Side	Terminal Accommodation	#14 AWG - #10 AWG
Number of Gangs	1	Throw Type	Single Throw
Amperage	15 A	Number of Poles	Single Pole
Requires Neutral Wire	Yes	Indoor/Outdoor	Indoor
Mounting Type	Wall Box	Location Rating	Dry
Wire Connection Type	Push Wire, Wire Terminal	Voltage	120 VAC, 125 VAC
Load Type	CFL, Fluorescent, Halogen, Incandescent, LED, Universal, Xenon	Environmental Conditions	UL94 V2