



radiant Collection
radiant® Momentary Contact Switch
Part No. TM870STMICC6



The radiant Registered Momentary Contact Switch is perfect anywhere you need the safety of a switch that is only on when held in the "on" position. Made exclusively for use with screwless Wall Plates from the radiant Registered Collection, sold separately.

Features & Benefits

- Part of the radiant® collection. High-impact resistant thermoplastic construction
- Narrow back body leaves more room for wires in the box. Extra-long, through-body strap eliminates floating installations and imperfect applications
- Smooth, quiet paddle action Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.

Specifications

General Info

Product Line	Pass & Seymour	Color	Ivory
Finish	Satin	UPC Number	785007043662
Country Of Origin	Mexico	Material	Thermoplastic
Features	Decorator Style, Momentary Contact	Switch Type	Paddle
Number of Switches	1	Application Sector	Residential
Wall Plate Included	No	Warranty Type	1-Year Limited Warranty
Type	Switch		

Dimensions

Product Width US	1.43 in	Product Depth US	1.27 in
Product Height US	4.19 in		
Listing Agencies / 3rd Party Agencies			
cULus Listed	Yes		
Additional Information			
Product Environmental Profile	Yes		
Technical Information			
Load Rating	15 A @ 120 VAC	Connection Location	Back and Side
Terminal Accommodation	#14 AWG - #10 AWG	Number of Gangs	1
Throw Type	Single Throw	Amperage	15 A
Number of Poles	Single Pole	Requires Neutral Wire	Yes
Indoor/Outdoor	Indoor	Mounting Type	Wall Box
Location Rating	Dry	Wire Connection Type	Push Wire, Wire Terminal
Voltage	120 VAC, 125 VAC	Load Type	CFL, Fluorescent, Halogen, Incandescent, LED, Universal, Xenon