



radiant Collection
radiant® 15A 3-Way Switch with Locator Light, Ivory
Part No. TM873ISLCC10



Perfect for use in larger rooms like master suites and foyers, this 3-way switch allows for control of a single light or fixture from two separate switches. It also includes a small, built-in light for easily locating in the dark. Part of the radiant Registered Collection, it features clean lines and smooth paddle action for a sophisticated touch. Made exclusively for use with screwless Wall Plates from the radiant Registered Collection, sold separately.

Features & Benefits

For use with incandescent lights/bulbs only.	Replaces any standard switch with ease, in as little as 10 minutes.
Locator light illuminates when switch is off, emitting a soft glow to help you find it in the dark. Locator light functions only when paired with an incandescent light.	Uses a paddle switch for smoother control with a low-profile aesthetic.
Features durable, high-impact resistant thermoplastic construction.	Designed to install easily with a narrower back body and captivated mounting screws.
More color options available to fit any style, including finishes to match current hardware and lighting trends.	Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.

Specifications

General Info

Product Line	Pass & Seymour	Color	Ivory
Finish	Satin	UPC Number	785007856507
Country Of Origin	China	Features	Locator Light
Switch Type	Paddle	Number of Switches	1
Application Sector	Commercial, Residential	Wall Plate Included	No
Warranty Type	1-Year Limited Warranty	Type	Switch

Dimensions

Product Width US	1.43 in	Product Depth US	1.27 in
Product Height US	4.19 in		
Listing Agencies / 3rd Party Agencies			
cULus Listed	Yes		
Technical Information			
Load Rating	15 A @ 120/125 VAC	Connection Location	Back and Side
Terminal Accommodation	#14 AWG - #10 AWG	Number of Gangs	1
Throw Type	Single Throw	Amperage	15 A
Number of Poles	3-Way	Requires Neutral Wire	Yes
Indoor/Outdoor	Indoor	Mounting Type	Box
Location Rating	Dry	Wire Connection Type	Push Wire, Wire Terminal
Voltage	120/125 V	Load Type	CFL, Fluorescent, Halogen, Incandescent, LED, Universal, Xenon