



radiant Collection  
**radiant® 15A 3-Way Switch, White, with Microban®**  
Part No. TM873WAMCC4



This switch features enduring Microban Registered antimicrobial technology that works to reduce the growth of bacteria, around the clock, for the lifespan of the product.

Allowing control of a light or fixture from two separately located switches, the radiant Registered 3-Way Switch with Microban upgrades your space with clean lines and smooth paddle action for a sophisticated touch.

Made exclusively for use with screwless Wall Plates from the radiant Registered Collection, sold separately.

This product is not currently available for sale in Canada.

## Features & Benefits

Helps fight the growth of stain and odor-causing bacteria through the invisible and continuous product protection of Microban® antimicrobial technology

Uses a paddle switch for smoother control with a low-profile aesthetic.

Features durable, high-impact resistant thermoplastic construction.

Complete the look with a sleek, screwless radiant® Wall Plate (also available with Microban), and coordinate with other designer switches and outlets available from the radiant® Collection.

Replaces any standard switch with ease, in as little as 10 minutes.

Allows you to control a light fixture from two locations in a room.

Designed to install easily with a narrower back body and captivated mounting screws.

## Specifications

### General Info

|                    |                         |                     |                          |
|--------------------|-------------------------|---------------------|--------------------------|
| Product Line       | Pass & Seymour          | Color               | White                    |
| Finish             | Satin                   | UPC Number          | 785007432510             |
| Country Of Origin  | China                   | Features            | Antimicrobial Protection |
| Switch Type        | Paddle                  | Number of Switches  | 1                        |
| Application Sector | Commercial, Residential | Wall Plate Included | No                       |
| Standard           | RoHS, CSA, UL, cULus    | Warranty Type       | 1-Year Limited Warranty  |

|                                       |                                              |                        |                                                                |
|---------------------------------------|----------------------------------------------|------------------------|----------------------------------------------------------------|
| Type                                  | Switch                                       |                        |                                                                |
| Dimensions                            |                                              |                        |                                                                |
| Product Width US                      | 1.43 in                                      | Product Depth US       | 1.27 in                                                        |
| Product Height US                     | 4.19 in                                      |                        |                                                                |
| Listing Agencies / 3rd Party Agencies |                                              |                        |                                                                |
| cULus ListingNumber                   | E140597                                      | cULus Listed           | Yes                                                            |
| Technical Information                 |                                              |                        |                                                                |
| Load Rating                           | 15 A @ 120/125 VAC                           | Seismic Tested         | No                                                             |
| Connection Location                   | Back and Side                                | Terminal Accommodation | #14 AWG - #10 AWG                                              |
| Throw Type                            | Single Throw                                 | Amperage               | 15 A                                                           |
| Number of Poles                       | 3-Way                                        | Requires Neutral Wire  | Yes                                                            |
| Indoor/Outdoor                        | Indoor                                       | Mounting Type          | Box                                                            |
| Location Rating                       | Dry                                          | Wire Connection Type   | Push Wire, Wire Terminal                                       |
| Voltage                               | 120/125 V                                    | Load Type              | CFL, Fluorescent, Halogen, Incandescent, LED, Universal, Xenon |
| Environmental Conditions              | 0 to 90% (relative humidity, non-condensing) |                        |                                                                |