



radiant Collection
radiant® 15A 4-Way Switch, Brown
Part No. TM874



For your largest or most open spaces, a radiant Registered 4-Way Switch enables control of a single light or fixture from three or more separate locations (working in conjunction with 3-Way Switches). Perfect for basements or multi-level rooms. Part of the radiant Collection, it features clean lines and smooth paddle action for a sophisticated touch. Made exclusively for use with screwless Wall Plates from the radiant Registered Collection, sold separately.

Features & Benefits

Replaces any standard switch with ease, in as little as 10 minutes

Uses a paddle switch for smoother control with a low-profile aesthetic

Features durable, high-impact resistant thermoplastic construction

Designed to install easily with a narrower back body and captivated mounting screws

More color options available to fit any style, including finishes to match current hardware and lighting trends

Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection

Back and side wire termination options accepts #14–#10AWG solid & stranded wires, Copper-clad aluminum, and copper wire

Specifications

General Info

Product Line	Pass & Seymour	Color	Brown
Finish	Satin	UPC Number	785007845020
Country Of Origin	Mexico	Material	Thermoplastic
Features	Decorator Style	Switch Type	Paddle
Number of Switches	1	Application Sector	Commercial, Residential
Wall Plate Included	No	Warranty Type	1-Year Limited Warranty
Type	Switch		

Dimensions

Product Width US	1.43 in	Product Depth US	1.27 in
Product Height US	4.19 in		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E140597	cULus Listed	Yes
---------------------	---------	--------------	-----

Additional Information

Product Environmental Profile	Yes
-------------------------------	-----

Technical Information

Load Rating	15 A @ 120 VAC	Connection Location	Back and Side
Terminal Accommodation	#14 AWG - #10 AWG	Number of Gangs	1
Throw Type	Single Throw	Amperage	15 A
Number of Poles	4-Way	Requires Neutral Wire	Yes
Indoor/Outdoor	Indoor	Mounting Type	Wall Box
Location Rating	Dry	Wire Connection Type	Push Wire, Wire Terminal
Voltage	120 VAC, 125 VAC	Load Type	CFL, Fluorescent, Halogen, Incandescent, LED, Universal, Xenon