



radiant Collection  
radiant® 15A 4-Way Switch with Locator Light, Light Almond  
Part No. TM874LASLCC6



With a radiant Registered 4-Way Switch, you can control a single light or fixture from three or more separate locations (working in conjunction with 3-Way Switches). Perfect for basements or multi-level rooms. Part of the radiant Collection, it features clean lines and smooth paddle action for a sophisticated touch. Made exclusively for use with screwless Wall Plates from the radiant Registered Collection, sold separately.

## Features & Benefits

|                                                                                                                                                                          |                                                                                                                                                                |
|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------|
| For use with incandescent lights/bulbs only.                                                                                                                             | Replaces any standard switch with ease, in as little as 10 minutes.                                                                                            |
| Locator light illuminates when switch is off, emitting a soft glow to help you find it in the dark. Locator light functions only when paired with an incandescent light. | Uses a paddle switch for smoother control with a low-profile aesthetic.                                                                                        |
| Features durable, high-impact resistant thermoplastic construction.                                                                                                      | Designed to install easily with a narrower back body and captivated mounting screws.                                                                           |
| More color options available to fit any style, including finishes to match current hardware and lighting trends.                                                         | Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection. |

## Specifications

### General Info

|                     |                                |                    |                         |
|---------------------|--------------------------------|--------------------|-------------------------|
| Product Line        | Pass & Seymour                 | Color              | Light Almond            |
| Finish              | Satin                          | UPC Number         | 785007242010            |
| Country Of Origin   | Mexico                         | Material           | Thermoplastic           |
| Features            | Decorator Style, Locator Light | Switch Type        | Paddle                  |
| Number of Switches  | 1                              | Application Sector | Commercial, Residential |
| Wall Plate Included | No                             | Warranty Type      | 1-Year Limited Warranty |
| Type                | Switch                         |                    |                         |

Dimensions

|                   |         |                  |         |
|-------------------|---------|------------------|---------|
| Product Width US  | 1.43 in | Product Depth US | 1.27 in |
| Product Height US | 4.19 in |                  |         |

Listing Agencies / 3rd Party Agencies

|              |     |
|--------------|-----|
| cULus Listed | Yes |
|--------------|-----|

Technical Information

|                        |                   |                       |                                                                |
|------------------------|-------------------|-----------------------|----------------------------------------------------------------|
| Load Rating            | 15 A @ 120 VAC    | Connection Location   | Back and Side                                                  |
| Terminal Accommodation | #14 AWG - #10 AWG | Number of Gangs       | 1                                                              |
| Throw Type             | Single Throw      | Amperage              | 15 A                                                           |
| Number of Poles        | 4-Way             | Requires Neutral Wire | Yes                                                            |
| Indoor/Outdoor         | Indoor            | Mounting Type         | Wall Box                                                       |
| Location Rating        | Dry               | Wire Connection Type  | Push Wire, Wire Terminal                                       |
| Voltage                | 120 VAC, 125 VAC  | Load Type             | CFL, Fluorescent, Halogen, Incandescent, LED, Universal, Xenon |