



Pass and Seymour  
TradeMaster® 3-Gang Nylon Wall Plate, 2 Toggle Switch Openings, 1 Duplex Receptacle Opening, Ivory  
Part No. TP28I



Trademaster Plate 3-Gang, 2-toggle, 1-duplex receptacle

## Features & Benefits

Molded of rugged, practically indestructible self-extinguishing nylon. (‘TP’ series only.)

Available in Ivory, White, Brown, Gray, Black, Blue, Orange, Red, and Light Almond.

Nominal thickness, .070 inch.

High Impact resistant nylon face.

Preferred for hospital, industrial, institutional, and other high-abuse applications.

## Specifications

### General Info

|                   |                                               |                    |                         |
|-------------------|-----------------------------------------------|--------------------|-------------------------|
| Product Line      | Pass & Seymour                                | Color              | Ivory                   |
| Finish            | Matte                                         | UPC Number         | 785007275155            |
| Country Of Origin | Mexico                                        | Material           | Nylon                   |
| Construction      | Plastic                                       | Wall Plate Size    | Standard Size           |
| Wall Plate Type   | Combination, Duplex Receptacle, Toggle Switch | Application Sector | Commercial, Residential |
| Standard          | CSA, UL514                                    | Warranty Type      | 1-Year Limited Warranty |
| Type              | Wall Plate                                    |                    |                         |

### Dimensions

|                   |           |                  |         |
|-------------------|-----------|------------------|---------|
| Product Width US  | 6.563 in  | Product Depth US | 0.25 in |
| Product Height US | 4.6875 in |                  |         |

### Listing Agencies / 3rd Party Agencies

|                     |        |              |     |
|---------------------|--------|--------------|-----|
| cULus ListingNumber | 143222 | cULus Listed | Yes |
|---------------------|--------|--------------|-----|

### Additional Information

Product Environmental Profile Yes

Technical Information

|                |          |                 |             |
|----------------|----------|-----------------|-------------|
| Thickness      | 0.07 in  | Number of Gangs | 3           |
| Indoor/Outdoor | Indoor   | Mounting Type   | Box Mounted |
| Orientation    | Vertical |                 |             |