



Pass and Seymour  
TradeMaster® 2-Gang Nylon Wall Plate, 2 Toggle Switch Openings, White  
Part No. TP2W



Trademaster Wall Plate 2-Gang 2toggle

## Features & Benefits

Molded of rugged, practically indestructible self-extinguishing nylon. ('TP' series only.)

Available in Ivory, White, Brown, Gray, Black, Blue, Orange, Red, and Light Almond.

Nominal thickness, .070 inch.

Available in 'TP' series, extra 3/16 inch width and height than Standard size plates: and 'TPJ' series, extra 3/16 inch width and height than Junior-Jumbo size plates.

Preferred for hospital, industrial, institutional, and other high-abuse applications.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

## Specifications

### General Info

|                   |                |                    |                         |
|-------------------|----------------|--------------------|-------------------------|
| Product Line      | Pass & Seymour | Color              | White                   |
| Finish            | Matte          | UPC Number         | 785007274134            |
| Country Of Origin | United States  | Material           | Nylon                   |
| Construction      | Plastic        | Wall Plate Size    | Standard Size           |
| Wall Plate Type   | Toggle Switch  | Application Sector | Commercial, Residential |
| Standard          | CSA, UL514     | Warranty Type      | 1-Year Limited Warranty |
| Type              | Wall Plate     |                    |                         |

### Dimensions

|                                       |           |                  |               |
|---------------------------------------|-----------|------------------|---------------|
| Product Width US                      | 4.75 in   | Product Depth US | 0.25 in       |
| Product Height US                     | 4.6875 in |                  |               |
| Listing Agencies / 3rd Party Agencies |           |                  |               |
| cULus ListingNumber                   | 143222    | cULus Listed     | Yes           |
| Additional Information                |           |                  |               |
| Product Environmental Profile         | Yes       |                  |               |
| Technical Information                 |           |                  |               |
| Thickness                             | 0.07 in   | Number of Gangs  | 2             |
| Indoor/Outdoor                        | Indoor    | Mounting Type    | Strap Mounted |
| Orientation                           | Vertical  |                  |               |