



Pass and Seymour
TradeMaster® 1-Gang Nylon Wall Plate, 0.625-in Round Opening, Ivory
Part No. TP60I



Singlegang,Single telephone or cable outlet 5/8-inch ID.Box mounted. Nylon Trademaster plate. .

Features & Benefits

Molded of rugged, practically indestructible self-extinguishing nylon. ('TP' series only.) Available in 'TP' series, extra 3/16 inch width and height than Standard size plates: and 'TPJ' series, extra 3/16 inch width and height than Junior-Jumbo size plates.

Available in Ivory, White, Brown, Gray, Black, Blue, Orange, Red, and Light Almond. Preferred for hospital, industrial, institutional, and other high-abuse applications.

Nominal thickness, .070 inch.

Specifications

General Info

Product Line	Pass & Seymour	Color	Ivory
Finish	Matte	UPC Number	785007534665
Country Of Origin	United States	Material	Nylon
Construction	Plastic	Wall Plate Size	Standard Size
Wall Plate Type	Coaxial, Round, Telephone	Application Sector	Commercial, Residential
Standard	CSA, UL514	Warranty Type	1-Year Limited Warranty
Type	Wall Plate		

Dimensions

Product Width US	2.9375 in	Product Depth US	0.25 in
Product Height US	4.6875 in	Circular Outlet Diameter	0.625 in

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Additional Information

Product Environmental Profile Yes

Technical Information

Thickness	0.07 in	Number of Gangs	1
Indoor/Outdoor	Indoor	Mounting Type	Box Mounted
Orientation	Vertical		