



OneGang Power Outlet Receptacle Opening, 1.5938 hole for 1.5625 diameter device -2 mtg. holes,White Nylon.



## Features & Benefits

Molded of rugged, practically indestructible self-extinguishing nylon. ('TP' series only.) Available in 'TP' series, extra 3/16 inch width and height than Standard size plates: and 'TPJ' series, extra 3/16 inch width and height than Junior-Jumbo size plates.

Available in Ivory, White, Brown, Gray, Black, Blue, Orange, Red, and Light Almond. Preferred for hospital, industrial, institutional, and other high-abuse applications.

Nominal thickness, .070 inch.

## Specifications

### General Info

|                   |                |                    |                         |
|-------------------|----------------|--------------------|-------------------------|
| Product Line      | Pass & Seymour | Color              | Brown                   |
| Finish            | Matte          | UPC Number         | 785007275872            |
| Country Of Origin | Mexico         | Material           | Nylon                   |
| Construction      | Plastic        | Wall Plate Size    | Standard Size           |
| Wall Plate Type   | Outlet, Round  | Application Sector | Commercial, Residential |
| Standard          | CSA, UL514     | Warranty Type      | 1-Year Limited Warranty |
| Type              | Wall Plate     |                    |                         |

### Dimensions

|                   |           |                          |           |
|-------------------|-----------|--------------------------|-----------|
| Product Width US  | 2.9375 in | Product Depth US         | 0.25 in   |
| Product Height US | 4.6875 in | Circular Outlet Diameter | 1.5938 in |

Listing Agencies / 3rd Party Agencies

|                     |        |              |     |
|---------------------|--------|--------------|-----|
| cULus ListingNumber | 143222 | cULus Listed | Yes |
|---------------------|--------|--------------|-----|

Additional Information

|                               |     |
|-------------------------------|-----|
| Product Environmental Profile | Yes |
|-------------------------------|-----|

Technical Information

|                |          |                 |               |
|----------------|----------|-----------------|---------------|
| Thickness      | 0.07 in  | Number of Gangs | 1             |
| Indoor/Outdoor | Indoor   | Mounting Type   | Strap Mounted |
| Orientation    | Vertical |                 |               |