



radiant Collection
radiant® 15W Weather-Resistant USB Outlet, Type A/C, 15A, Tamper-Resistant, Light Almond
Part No. WRR26USBAC6LA



Charge phones, tablets and more up to 40% faster, anywhere, with the Outdoor USB Outlet from the radiant® Collection. With an industry-leading 27W of power supplying the built-in USB Type-A and USB Type-C connections, this outlet helps you get that full battery feeling with convenience and speed – no bulky adapters needed. Easy to install and featuring the sleek, clean lines of radiant, the Outdoor USB Outlet is engineered for weather* resistance to add advanced functionality to your patio, pool area, deck or porch. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.

Features & Benefits

Designed with weather-resistance for use in outdoor locations such as decks, patios and pool areas. *Must be installed in weatherproof enclosure per NEC requirements.

Provides fast and convenient built-in charging, without sacrificing plugs or requiring a bulky adapter.

Features an industry-leading 6.0A of power, as well as Smart Chip technology, to maximize charging speed for each USB connection.

Includes connections for both traditional USB Type-A and the newer USB Type-C , to accommodate all mobile devices.

All Legrand USB Outlets are manufactured through high-quality design, sourcing and production, and backed by a Lifetime Warranty.

Protects children with a patented tamper-resistant shutter system that prevents improper insertion of foreign objects, complete with "invisi-shutters" for an invisible effect.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.

Specifications

General Info

Product Line	Pass & Seymour	Color	Light Almond
Finish	Satin	UPC Number	785007249378
Country Of Origin	China	Number of Receptacles	2
Features	USB-A Charging, USB-C Charging, Weatherproof	Outlet Type	Tamper-Resistant, USB-Charging, Weather-Resistant
Application Sector	Hospitality, Multi-Dwelling Unit, Residential	Wall Plate Included	No
Warranty Type	Limited Lifetime Warranty		

Dimensions

Product Width US	1.693 in	Product Depth US	1.35 in
------------------	----------	------------------	---------

Product Height US	2.677 in
-------------------	----------

Technical Information

Connection Location	Back and Side	USB Wattage	15 W
USB Amperage	6 A	Number of USBs	2
Number of Wires	3	Amperage	15 A
Number of Poles	Double Pole	Indoor/Outdoor	Outdoor
NEMA Configuration Code	5-15R	Mounting Type	Box
Wire Connection Type	Internal Pressure Plates, Screw Terminals	Voltage	5.0 V