



radiant Collection

radiant® 15W Weather-Resistant USB Outlet, Type A/C, 15A, Tamper-Resistant, White

Part No. WRR26USBAC6W



Charge phones, tablets and more up to 40% faster, anywhere, with the Outdoor USB Outlet from the radiant® Collection. With an industry-leading 27W of power supplying the built-in USB Type-A and USB Type-C connections, this outlet helps you get that full battery feeling with convenience and speed – no bulky adapters needed. Easy to install and featuring the sleek, clean lines of radiant, the Outdoor USB Outlet is engineered for weather* resistance to add advanced functionality to your patio, pool area, deck or porch. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.

Features & Benefits

Designed with weather-resistance for use in outdoor locations such as decks, patios and pool areas. *Must be installed in weatherproof enclosure per NEC requirements.	Provides fast and convenient built-in charging, without sacrificing plugs or requiring a bulky adapter.
Features an industry-leading 6.0A of power, as well as Smart Chip technology, to maximize charging speed for each USB connection.	Includes connections for both traditional USB Type-A and the newer USB Type-C , to accommodate all mobile devices.
All Legrand USB Outlets are manufactured through high-quality design, sourcing and production, and backed by a Lifetime Warranty.	Protects children with a patented tamper-resistant shutter system that prevents improper insertion of foreign objects, complete with "invisi-shutters" for an invisible effect.
More color options available to fit any style, including finishes to match current hardware and lighting trends.	Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Finish	Satin	UPC Number	785007249392
Country Of Origin	China	Number of Receptacles	2
Features	USB-A Charging, USB-C Charging, Weatherproof	Outlet Type	Tamper-Resistant, USB-Charging, Weather-Resistant
Application Sector	Hospitality, Multi-Dwelling Unit, Residential	Wall Plate Included	No

Warranty Type	Limited Lifetime Warranty		
Dimensions			
Product Width US	1.693 in	Product Depth US	1.35 in
Product Height US	2.677 in		
Technical Information			
Connection Location	Back and Side	USB Wattage	15 W
USB Amperage	6 A	Number of USBs	2
Number of Wires	3	Amperage	15 A
Number of Poles	Double Pole	Indoor/Outdoor	Outdoor
NEMA Configuration Code	5-15R	Mounting Type	Box
Wire Connection Type	Internal Pressure Plates, Screw Terminals	Voltage	5.0 V
Environmental Conditions	95% (relative humidity, non-condensing)		