



Wattstopper
Power Pack, 120-277V, 50/60Hz, 24VDC, 225mA, RJ45 Connector
Part No. BZ-50RC



The BZ-50 Universal Voltage Power Pack provides 24 VDC operating voltage to Wattstopper's low-voltage occupancy sensors. This device is constructed with environmentally friendly materials and is RoHS-compliant.

Features & Benefits

Self-contained power supply relay system

Efficient switching power supply providing optimized current output based on number of sensors

LED indicates status of relay or if there is a low-voltage overcurrent

The product meets the materials restrictions of RoHS

Zero crossing circuitry for reliability and increased product life

UL 2043 plenum rated for cost-effective installation

1/2" snap-in nipple attaches to standard electrical enclosures through 1/2" knockouts

Specifications

General Info

Product Line	Wattstopper	Color	Gray
UPC Number	754182923496	Country Of Origin	China
Material	ABS	Product Series	BZ
Installation Location	Ceiling	Application Sector	Commercial
Warranty Type	5-Year	Type	Power Pack

Dimensions

Product Width US	2.8 in	Product Weight US	0.3 lb
Product Volume US	28.1 cu in	Product Depth US	1.7 in

Product Height US	2.2 in
-------------------	--------

Additional Information

RoHS Compliant	Yes
----------------	-----

Technical Information

Operating Temperature Min	32 °F	Output Voltage	24 VDC
Wire Gauge	18-22 AWG	Operating Temperature Max	104 °F
Input Voltage	120/277 VAC, 230/240 VAC	Line Frequency	50 Hz, 60 Hz
Indoor/Outdoor	Indoor	Mounting Type	1/2 in Knockout
Operating Temperature	32°-104°F	Operating Humidity	5-95% RH (Non-Condensing)
Wire Connection Type	RJ-45	Connection Type	Wired