



Pass and Seymour
WattStopper® High Bay Lens with Masking Coverage 30ft x 20ft at 40ft Height
Part No. HBL1M



The HBL1M Lens customized coverage is ideal for the beginning of aisle ways where cross traffic could be an issue. The HBL1M comes with opaque adhesive tape applied to the interior of the lens, cutting off 1/2 of the coverage pattern. 30' x 20' HBL1M coverage when mounted at 40' height.

Features & Benefits

30' x 20' HBL1M coverage when mounted at 40' height

Ideal for high ceiling aisleway applications

Multi-cell, multi-tier Fresnel lenses

Specifications

General Info

Product Line	Pass & Seymour	UPC Number	754182921904
Country Of Origin	China	Switch Type	Motion Sensor

Dimensions

Product Width US	3.7 in	Product Height US	1.4 in
Product Length US	3.7 in		

Technical Information

Operating Temperature Min	32 °F	Seismic Tested	No
Sensor Type	Occupancy	Operating Temperature Max	131 °F
Wire Size	#14 - #10 AWG	Operating Temperature	0°-55°C, 32°-131°F
Location Rating	Wet		