



Pass and Seymour
WattStopper® High Bay Lens Coverage 48ft Diameter at 10ft Height
Part No. HBL2



For low bay applications, the HBL2 pattern spreads over a 48' diameter area at a height of 8'. This lens offers 360 Degree coverage and are best suited for open area and aisleway coverage in high bay applications. This is a multi-cell, multi-tier Fresnel lens offers a high density coverage pattern.

Features & Benefits

48' diameter coverage when mounted at a 8' height

Ideal for high ceiling open area and aisleway coverage in high bay applications

Multi-cell, multi-tier Fresnel lenses

Specifications

General Info

Product Line	Pass & Seymour	UPC Number	754182925223
--------------	----------------	------------	--------------

Country Of Origin	China	Switch Type	Motion Sensor
-------------------	-------	-------------	---------------

Dimensions

Product Width US	3.66 in	Product Height US	1.09 in
------------------	---------	-------------------	---------

Product Length US	3.66 in
-------------------	---------

Technical Information

Operating Temperature Min	32 °F	Seismic Tested	No
---------------------------	-------	----------------	----

Sensor Type	Occupancy	Operating Temperature Max	131 °F
-------------	-----------	---------------------------	--------

Wire Size	#14 - #10 AWG	Operating Temperature	0°-55°C, 32°-131°F
-----------	---------------	-----------------------	--------------------

Location Rating	Dry
-----------------	-----