



For wet locations, low bay applications, the HBL2 pattern spreads over a 48' diameter area at a height of 8'. This lens offers 360 Degree coverage and are best suited for open area and aisleway coverage in high bay applications. This is a multi-cell, multi-tier Fresnel lens offers a high density coverage pattern.

Features & Benefits

48' diameter coverage when mounted at a 8' height

Ideal for high ceiling open area and aisleway coverage in high bay applications

Multi-cell, multi-tier Fresnel lenses

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Finish	Matte	UPC Number	754182925230
Country Of Origin	China	Switch Type	Motion Sensor

Dimensions

Product Width US	3.66 in	Product Height US	1.09 in
Product Length US	3.66 in		

Technical Information

Operating Temperature Min	32 °F	Seismic Tested	No
Sensor Type	Occupancy	Operating Temperature Max	131 °F
Wire Size	#14 - #10 AWG	Operating Temperature	0°-55°C, 32°-131°F
Location Rating	Wet		