



The LMFC-xRJ provides fixture connectivity to the DLM local network via a single- or dual-port RJ45 wiring whip connector. The dual-port is best for daisy chaining multiple fixtures together. Each DLM local network can support up to 64 loads.

Features & Benefits

Separate single- or dual-port RJ45 connector mounts on fixture housing, and provides connectivity to DLM local network

Specifications

General Info

Product Line	Wattstopper	Color	White
UPC Number	754182939015	Country Of Origin	China
Material	Polycarbonate	Product Series	LMFC
Features	Flame Retardant, Impact Resistant, UV Grade	Installation Location	Fixture
Works With	DLM Fixture Controller	Application Sector	Commercial
Standard	UL, cUL, RoHS	Warranty Type	5-Year
Type	Interface		

Dimensions

Product Width US	1.5 in	Product Weight US	0.13 lb
Product Volume US	2.9 cu in	Product Depth US	0.8 in
Product Height US	2.4 in		

Additional Information

RoHS Compliant	Yes	Security	Yes
----------------	-----	----------	-----

Technical Information

Operating Temperature Min	32 °F	Number of Connections	2
Operating Temperature Max	158 °F	Indoor/Outdoor	Indoor
Mounting Type	Snap-in	Connector 2	RJ-45 Male
Connector 1	RJ-45 Male	Operating Temperature	0°-70°C, 32°-158°F
Operating Humidity	5-95% RH (Non-Condensing)		